



902

Water Activated Tape Semi-Automatic Random Case Sealer



Random Case Sealing

The machine will measure the case and automatically adjust the upper taping unit and drive belts to size using motors and encoders. Cases are then sealed top and bottom, throughout the size range in any random sequence. The 902 can operate on small, large, lightweight or heavy cases.



Water Activated Tape System

Once the case is moved into the taping area the 3-channel water system will supply water to the tape on the top and bottom taping heads. The taping heads will then apply the tape to the case. Brushes at the exit are used for a good adhesion of the tape.



Robust Construction

High quality components housed in a robust chassis ensure minimal servicing and enable 24 hour operation. Designed for the rigours of typical end-of-line packaging environments.



Compact

The Endoline 902 is well suited to environments where there is insufficient space for multiple sealers or there are regular case size changes



Safety

The machine is designed to the latest UKCA & CE regulations and meets all safety requirements. The machine has a lift up guard door fitted with gas struts, that will stop the machine immediately if opened.



Ease of Operation

Simple mechanical operation and clear access for easy cleaning and maintenance make this an efficient and straightforward machine to operate. Fitted as standard with a roller infeed table and castors.






902

Water Activated
Tape Semi-Automatic
Random Case Sealer

Machine includes:

- Water pumping system for glue activation including 5-litre water tank.
- Low water sensor with visual alarm.
- 3-channel water recycling system.
- 6 bar pneumatic air management system, with adjustable safety pressure switch.
- Pneumatic movement system, allowing quick and safe replacement of bottom tape reel.
- 7" colour touchscreen display.

902 dimensions shown



Case Dimensions (mm).

	Length	Width	Height
Maximum	800mm	600mm	600mm
Minimum	250mm	150mm	150mm

Note:

- Machine can be modified for cases outside case size range. Please contact Endoline to advise.

Speed

- Up to 14 cases per min

Pneumatics

- 6 bar Pneumatics air management system

Electrical

- 230V 1-P +N +GND/50Hz

Machine Finish

- Mild steel, powder coated white

Seal Method

- Water Activated Tape.

© Endoline reserves the right to change specifications without prior notice.

Endoline Machinery Limited

Stratton Business Park, London Road Biggleswade, Bedfordshire SG18 8QB United Kingdom
Telephone: +44 (0) 1767 316422 Facsimile: +44 (0) 1767 318033 E-mail: sales@endoline-automation.com

